

2004-2005



Assistive Listening Devices

www.williamssound.com



Williams Sound[®]
Helping People Hear

Sold by:



<http://www.TWAcomm.com>
Toll Free: (877) 892-2666



Amplified Phones

No one should have to struggle when it comes to hearing on the telephone. Listen more easily and clearly with these amplified phones from Williams Sound:

Model TEL 040



TELETALKER®

- 55 dB of strong amplification
- Improves speech understanding
- Amplifies calls without feedback
- Extra loud ringer, flashing ring indicator
- Easy-to-use buttons & volume control
- Compatible with telecoil-equipped hearing aids
- 5 YEAR WARRANTY*

Strongest amplification available on the market!

PhoneMax®

- 25 dB of amplification
- Makes speech more understandable
- Extra loud ringer
- Flashing ring indicator
- Easy-to-use buttons & volume control
- Compatible with telecoil-equipped hearing aids
- 5 YEAR WARRANTY*


Exceptional price, exceptional value!



Model TEL 030



Model TEL 008



RINGMAX® – Amplified Call Ringer

- 95 dB of amplification
- Amplifies the phone ring for better hearing
- Four selectable tone settings
- Adjustable volume control
- Mounts easily on to the wall
- Perfect for the shop, garage, or other noisy environments
- Use with multiple phones
- Includes flashing light ring indicator
- Operates on 4 AA batteries
- One year warranty

Don't miss important phone calls!

Sold by:



Pocketalker Pro™

When hearing situations prove most challenging, the Pocketalker delivers. Compact enough to bring anywhere, the Pocketalker is ideal for 1-on-1 conversations, TV listening, small groups, and much more.

- Amplifies sound for better understanding
- Compact, portable listening device
- Easy to use, battery operated
- Includes a plug-in sensitive microphone
- TV listening extension cord included
- Use with neckloops & telecoil - equipped hearing aids
- Clear, high quality sound
- 100 hours of long-lasting battery life
- 5 YEAR WARRANTY*

AN AMERICAN CLASSIC



● Includes Attractive Carrying Case



Optional Listening Accessories:



EAR 008



EAR 013



EAR 014



HED 021



HED 026




Hear more clearly and easily!



Use the Pocketalker with your telephone! Listen to calls at a comfortable level with a TELELINK adapter from Williams Sound.

TEL 001



Personal FM Systems

Eliminate background noise and other distractions. Ensure that the speaker's message is heard by everyone. Try a Personal FM System from Williams Sound. It's perfect for classrooms, job training, consultation and more.

HOW IT WORKS

The message is transmitted by an FM radio signal



Speaker talks into the transmitter's mic



Listeners wear receivers

THE RESULT:

The message is heard by **everyone**, even by those in the back of the room!

Hearing Helper® PFM 350

- Maximizes a student's ability to listen
- Portable, no wires, no hassle
- Hear more clearly in noisy environments
- Overcomes distance from speaker to listener
- Has a range of up to 150 feet
- Will operate up to 60 hours at a time
- May be used with telecoil-equipped hearing aids

5 YEAR WARRANTY*

Versatile, high-powered FM technology!



R31 Receiver

The R31 receiver features a sensitive **environmental microphone**. This gives the listener more flexibility on what they want to hear. By turning on the environmental mic, they can listen to a nearby classmate speak more clearly.



T30 Transmitter

Hearing Helper® PFM 300

- Same great features as the PFM 350 model - without the environmental mic on the receiver.

Super technology, super price!



Each System Includes:				Optional Microphones:	
					
Mini-Earphone (EAR 013)	Clip-on Microphone (MIC 090)	System Carrying Case	Receiver/Transmitter Case	Head-band Microphone (MIC 086)	Collar Microphone (MIC 085)

SoundPlus® Infrared Listening Systems

Infrared listening systems are perfect for TV and stereo listening, small groups, language interpretation, offices and more. Listen at the volume of your comfort, without disturbing anyone else.

5 YEAR WARRANTY



Model WIR 952

WIR 952 Stereo Infrared Listening System

- Super high-quality audio
- Comfortable, lightweight, under-the-chin style receiver
- Plugs directly into your TV, VCR, or stereo
- Operates up to 30 ft. from the receiver
- Receiver recharges itself when placed back on top of the transmitter. *It will always be charged when you need it!*
- Automatically shuts off when not in use.
- Operates on 95 kHz, stereo, or 250 kHz. Use your infrared receiver at the movies, theater, and other 95 KHz venues.
- **5 YEAR WARRANTY ***

HOW IT WORKS

The TX295 transmitter connects directly to your television, VCR, or other sound source.



Invisible Infrared Audio Signal



Listeners wear the wireless RX295 receiver to listen to the program!

Sold by:



Want a different receiver to use with your infrared system? Check out the WIR 125 listening system:

Model WIR 125

TX295 transmitter + RX3 Receiver.



Includes EAR 013 Earbud



Optional Accessories:




HED 021
Deluxe Headphone



HED 026
Deluxe Rear-Wear Headphone



EAR 022
Surround Earphone



NKL 001
Neckloop

The **WIR 125** system features the versatile RX3 receiver. The RX3 has an earphone jack which allows the user to plug in a variety of earphones, headphones, and other listening accessories (see optional accessories on right). It operates on a 9V alkaline battery for 35 hours of listening enjoyment.

Sold by:

 **TWAcomm.com**
http://www.TWAcomm.com
Toll Free: (877) 892-2666

MORE THAN JUST PRODUCT . . .



Williams Sound offers **CHOICES.**

Select an accessory that meets your needs:



EAR 013

Single Mini Earbud

Fits in the outer part of the ear.



EAR 014

Dual Mini Earbud

Fits in the outer part of the ear.



EAR 008

Wide Range Earphone

Hangs on the outside of the ear.



EAR 022

Surround Earphone

Hangs on the ear.



HED 021

Deluxe Folding Headphone

Features folding earpieces and single cord with mono 3.5 m plug.



HED 026

Deluxe Rear-Wear Headphone


Single cord with mono 3.5 m plug.



MIC 086


Headband-Style Microphone

Directional (electret) microphone with 39" cord and 3.5mm plug.



Neckloop Telecoil Coupler

Magnetically couples audio output with T-coil equipped hearing aid, telephone, or induction earphone.



BAT KT5

3V Multi-Charger Kit

Includes 3V Multi Charger, 4-AA NiMH Batteries. For use with PFM 300/350 System.

*90 day warranty on accessories

BRO 032C

1-800-843-3544 • www.williamssound.com